



DESCRIPTION	SR30-30V	SR60-60V				
Weight (Empty)	260 lb	510 lb				
Weight (Full)	366 lb	612 lb				
Dimensions standalone (H x W x D)	63¼" x 26¼" x 25¾"	77½" x 30¼" x 31³/8"				
Dimensions with vacuum (H x W x D)	63¼" x 43" x 25¾"	77½" x 30¼" x 80³/8"				
Boiler						
Volume	12 US gal (45 L)	25 US gal (95 L)				
Working capacity	7.5 US gal (30 L)	16 US gal (60 L)				
Material	304 stainless steel	304 stainless steel				
Wall thickness	1/8"	1/8"				
Oil jacket	1"	1"				
Insulation (wall/cone)	4"	4"				
Inside diameter	14"	20''				
Fill line	1"	1"				
Pressure relief system	1.5 psi	1.5 psi				
Rated for full vacuum to 100 psig. internal pressure to 600° F / 315° C.						



DESCRIPTION		SR30-30V	SR60-60V		(COMMON)	
Distillation rate (gal/h)		1.5 to 2.5	4 to 6		of Toluene, MEK or Acetone. Other solvents vary depending on heat of vaporization	
Assembly requireme	ent	The SR30 and 60 are assembled as one complete unit and tested our factory. Disassembled into (2) separate pieces: (1) the recycler are (1) the vacuum tank (option). The customer is responsible for providing electricity, compressed air, piping from the dirty solvent tank and piping to the clean solvent tank unless the optional hose kit was purchased				
Clearance requireme	nts	1 foot above and around the unit.				
Utilities required : Electricity		11 A, 200- 240 V,	24 A, 200- 240 V,	1 Ph. 6	n. 60 Hz	
Vacuum options		Compressed Air : 90 psig, 8 scfm, ¼" diameter, NPT.				
Heater		2.5 kW	5 kW		ric-resistance heater. (200° F to 550° Il fittings and motors are Class 1, Div. 1, up D	
Operating pressur	re	Ambient to 450° F				
Operating temperat	erating temperature		Atmospheric to full vacuum (22" – 27.5" of mercury).			
Heat up time		30 - 45 minutes.				
Cool down time		60 minutes. (can be longer depending on the type of solvent treated).				
Feed		Manually or by an optional diaphragm pump.				
Vacuum		Vacuum pump : air operated, requires clean air 80 psi, 5 cfm.				
Pressure relief		1.5 psi on the cover with progressive release of the over pressure.				
Controls		Microprocessor controlled. Unit is enclosed in an explosion proof container and is certified to operate in a Class 1, Div. 1, Group D environment.				
Instrumentation		Distillate / sludge, oil, cycle status, and safety status readings.				
Shipping data	30 >	32 x 32 x 69	44 x 48 x 86	< 60	(M/d vH) (:h)	
	30V >	32 x 48 x 69	48 x 48 x 86	< 60V	(WxLxH) (inches)	
Shipping Weight	30 >	385	610	< 60	<i>n</i> : >	
	30V >	445	820	< 60V	(lb)	
Certification	CSA certified USA and CAN, Class 1, Div. 1, Group D. All ISTpure recyclers meet the following NFPA¹ codes (30, 33, 70).					







346 Allée du Golf

St-Eustache, Quebec J7R 0M8 Canada